



Core Alignment fusion splicer

T-57C+

Powered by



NanoTune™
Enhanced splice experience



SumiCloud™



Power through with ease



Proven field toughness



High environmental resistance



Smart and ease



Reduce work time
Splicing 6s
Heating 15s

Specifications

Item		T-57C+
Optical fibre requirements	Material	Silica glass
	Fibre count / Profile types	Single / SMF(G.652), MMF(G.651), DSF(G.653), NZDSF(G.655), BIF(G.657)
	Fibre diameter	Cladding diameter : 80 ~ 150µm, Coating diameter : 100 ~ 1,000µm
	Cleave length	5 ~ 16mm with coating clamp
Standard performance	Splice loss (typical)*1	SMF : 0.02dB, MMF : 0.01dB, DSF : 0.04dB, NZDSF : 0.04dB, BIF : 0.02dB
	Return loss (typical)	60dB or greater
	Splice time (typical)	6sec(SM G652 Quick Mode), 8sec(Auto Mode)
	Heating time (typical)	15sec (FPS-61-2.6 sleeve, S60mm 0.25)
	Splice & Heat cycles per battery full charge*2	Approx. 310 (BU-16)
	Fibre view & magnification	2 CMOS cameras observation, 350X (zoom : 700X) for X or Y single axis view. 270X for both X & Y dual axis view
	Proof test	1.96 ~ 2.09N
Programs	Applicable protection sleeve	60mm, 40mm & Sumitomo Nano sleeves
	Splice programs	Max. 300, 40 are pre-optimised, 260 editable by user
	Heating programs	Max. 100, 23 are pre-optimised, 77 editable by user
Functions	Splice image capture / Splice data storage	200 images / 10,000 splice data (internal memory only) 50,200/20,000 (with 16GB SD card)
	Multi clamps	Provided, 250µm, 900µm tight & loose buffer fiber, 2&3mm jacket cord and rectangular drop cable, 3.5mm round drop cable
	Reversible coating clamps	Provided
	Onboard user training video	Provided
	Automatic fibre identification	SMF / MMF / DSF / NZDSF / BIF / Other
	Automatic arc calibration	Automatically compensates for environmental condition changes
	Display of remaining Splice & Heat cycles	Provided (Battery mode)
Size / Weight	Wireless LAN connectivity (Option)*3	Provided
	Size	128(W) x 154(D) x 130(H) mm (without anti-shock rubber)
	Weight	1.7kg (without Battery) / 2.1kg (with Battery BU-16)
	Monitor	5.0" touch screen color LCD display
Terminals	DC output	DC 12V (for JR-6+)
	USB port	USB 2.0 (mini-B type)
	Storage media	SD / SDHC memory card MAX32GB
Power supply	AC input	AC 100 ~ 240V, 50/60Hz (ADC-16)
	DC input	DC 10 ~ 15V
	Battery pack	Li-ion 10.8V, 6,400mAh (BU-16)
Operating condition	Altitude : 0 ~ 6,000m, Temperature : -10 ~ +50°C, Humidity : 0 ~ 95% (non-condensing), Wind velocity : up to 15m/sec	
Storage condition	Temperature : -40 ~ +80°C, Humidity : 0 ~ 95% (non-condensing), Battery : -20 ~ +30°C (long term)	
Electrode life *4	6,000 arc discharges	
Software updates	Internet	
Data management	Can be stored, edited and analyzed by dedicated PC software	

* 1: Average value of the final inspection in room temperature with Sumitomo identical fibre. Measured by cut-back method relevant to ITU-T and IEC standards.

* 2: Splice & Heat cycles may vary depending on the battery status and the operating environment.

* 3: Wireless LAN connectivity is not available in all countries. For more details, check our website. <http://global-sei.com/sumitomo-electric-splacers/emea/products/sumicloud/>

* 4: Achieved in lab condition. Electrode life may vary depending on the operating environment.

Environmental Durability*

Test details	
Shock resistance	Drop from 76cm on 5 faces(excluding top face), 4 edges and corners(bottom face only)
Impact resistance	Equivalent to IK07 on LCD monitor
Water resistance	Equivalent to IPx2
Dust resistance	Equivalent to IP5x

* Splicer operation after shock, impact, water or dust tests, was confirmed under battery power, by Sumitomo.
Does not guarantee the product will not be damaged by these conditions.

Basic Accessories

Part name	Part No.	Qty.
AC adapter	ADC-16	1 pc
AC power cord	PC-AC<X>*	1 pc
Cooling tray	—	1 pc
Spare electrode	ER-10	1 pair
Quick reference guide	—	1 pc
Carrying case with worktable	CC-72	1 pc
Hand strap	—	1 pc
USB cable	—	1 pc

* X=2(USA), 3(EU), 5(UK/HK), 6(AUS), 7(SOUTH AFRICA)

Items listed in the table are typical contents included with the splicer body. Overall kit content may vary regionally. Please check with your local authorised reseller to confirm kit content in your region.

Accessories

		Part name	Part No.	Remarks
Accessories for Splicer	Fibre holder	FHS-025	For ϕ 0.25mm single fibre	
		FHS-09	For ϕ 0.9mm single fibre	
		FHS-025/LB5	For 0.9mm loose buffered single fibre	
		FHD-1	For indoor / outdoor rectangular drop cable	
		1SM-ST	For indoor rectangular drop cable	
		FHC-3	For 3mm cable	
		Lynx2-UML-S	For ϕ 3mm cord and ϕ 0.9mm single fibre	
Accessories	Battery pack	BU-16	Li-ion 6,400mAh	
	Battery charger	BC-16	—	
	Car battery cable	PCV-16	Vehicle 12V outlet	
	Electrode	ER-10	—	
	Handheld cleaver	FC-8R-FC	Automatic blade rotation cleaver with counter	
	Bench-top Cleaver	FC-8R-F	Automatic blade rotation cleaver (no counter)	
	Jacket remover	FC-6R+ FC-6S+	Auto blade rotation Single fibre cleaver	
Accessories	Jacket remover	JR-M03	Jacket remover for single fibre	
	Loose tube cutter	LTC-01	—	
	Alcohol dispenser	HR-3	—	
	Fibre protection sleeve	FPS-1	60mm, diameter after shrink approx. ϕ 3.2mm	
		FPS-40	40mm, diameter after shrink approx. ϕ 3.2mm	
FPS-61-2.6		61mm, diameter after shrink approx. ϕ 2.6mm		



Carrying case with worktable
CC-72



Handy cleaver
FC-8R series



Bench-top cleaver
FC-6+ series



Jacket remover
JR-M03



Available for Lynx-Custom Fit™
Splice-On Connector



Electrode
ER-10

 Sumitomo Electric Industries, Ltd.